

Electronic Crockmeter YM-571

Usage:

Will be placed in the friction slip of paper machine, pressure b clamp, with dry and wet rubbing cloth friction after staining or discoloration was evaluated with grey cloth or friction specimen sample card. Test for colour fastness to dry and wet

friction of textile printing and dyeing.

Standard: GB/T3920 , AATCC 8/165, BS EN ISO 105,JIS L0849



ITOKIN2000



SPECIFICATION

Friction Type	Electronic
Times Setup	Any Times
Friction Range	104 mm +- 3 mm
Friction Rate	60/m
Friction Force	9N
Friction Probe	16 mm Round Copper